

Positionieren:
Lineare Bewegung:
Bogen Uhrzeigersinn:
Bogen Gegenuhrzeigersinn:
Reihenfolge:
Wiederholen:

Werkzeugliste

Datei Ansicht Sortieren

Nr.	Name	Ø	Z+	F(xy)	F(z)	S				
1	Balsa 1 mm LSV 1.2mm	1.20mm	1.00mm	1200mm/min	150mm/min	20000upm	90%	180.00°		
2	Balsa 1.5 mm LSV 1.2mm	1.20mm	1.50mm	1100mm/min	150mm/min	20000upm	90%	180.00°		
3	Balsa 2 mm LSV 1.2mm	1.20mm	2.00mm	1000mm/min	150mm/min	20000upm	90%	180.00°		
4	Balsa 2.5 mm LSV 1.2mm	1.20mm	2.50mm	900mm/min	150mm/min	20000upm	90%	180.00°		
5	Balsa 3 mm LSV 1.2mm	1.20mm	3.00mm	900mm/min	150mm/min	20000upm	90%	180.00°		
6	Balsa 4 mm LSV 1.2mm	1.20mm	4.00mm	800mm/min	150mm/min	20000upm	90%	180.00°		
7	Balsa 5 mm LSV 1.2mm	1.20mm	5.00mm	700mm/min	150mm/min	20000upm	90%	180.00°		
8	Balsa 6 mm LSV 1.2mm	1.20mm	6.00mm	600mm/min	150mm/min	20000upm	90%	180.00°		
9	Balsa 8 mm LSV 2mm	2.00mm	4.00mm	650mm/min	150mm/min	20000upm	90%	180.00°		
10	Balsa 10 mm LSV 2mm	2.00mm	5.00mm	600mm/min	150mm/min	20000upm	90%	180.00°		